












DW TECH BULLETIN

DOC#: DW11242010

Distribution: Internal

November 24, 2010

subject: Value Line Bullet Camera
OSD Menu Tree

EXPOSURE		MOTION (OMNI-Plus Camera Only)	
	LENS DC / MANUAL; Default is DC Lens.		ALARM OFF / ON
	ELC LEVEL ELC (Electronic Light Control) 0 ~ 100; Default is 40.		SET WINDOW
	DC LEVEL DC (Direct Drive) 0 ~ 31; Default is 17.		ALL SET
	E. SHUTTER 1/60 ~ 1/100000 / 1/100 FLC; Default is 1/60.		ALL CLEAR
	BLC OFF / ON		SENSITIVITY (0 ~ 55); Default is 44.
	SET LEVEL (BLC Setting)		SHOW INDICATOR (OFF / Icon / TRACE)
	AGC OFF / 12db ~ 36db; Default is 36db.		DELAY OUT (1 ~ 15)
	COLOR		PRIVACY
	WB MODE AWC / ATW / MANUAL / PUSH LOCK / MANUAL		MASK 1 OFF / ON . SET WINDOW
	M.WB R White Balance Manual Red Adjustment 0 ~ 255		MASK 2 OFF / ON . SET WINDOW
	M.WB B White Balance Manual blue Adjustment 0 ~ 255		MASK 3 OFF / ON . SET WINDOW
	R - Y GAIN 0 ~ 255		MASK 4 OFF / ON . SET WINDOW
	B - Y GAIN 0 ~ 255		COLOR SET BLACK / GRAY / COLOR 1 ~ 6
	DAY & NIGHT		SYNC
	D&N MODE AUTO / COLOR / B & W		SYNC MODE INTERNAL / AUTO
	BURST OFF / ON (for Day & Night Auto Mode)		V-PHASE 0 ~ 199
	COLOR to BW N/A		
	BW to COLOR N/A		SETUP
	READ TIME 3 ~ 12 (Time Delay to switch from Color to Black and White); Default is 3.		CAMERA ID 0 ~ 255
	FUNCTION		TITLE EDIT
	MIRROR OFF / ON		TITLE RESET
	SHARPNESS 0 ~ 49		TITLE Position Top-L / Top-R / Bottom-L / Bottom-R
	GAMMA 0.05 ~ 1.00 / USER; Default is 0.45.		DPC Set OFF/ON
	SLC OFF / ON		White Threshold 0 ~ 254
	SLC SET LEVEL 0 ~ 50		BLACK Threshold 0 ~ 254
	HME HME (Highlight Masking Exposure) OFF / ON		DPC LEVEL 0 ~ 254
	HME SET LEVEL 0 ~ 55		LANGUAGE English / Chinese
	DRC OFF / ON DRC (Dynamic Range Compressor)		PC Control ON / OFF
			EXIT
			EXIT / SAVE & EXIT / FACTORY SET

The 540 TV Line Resolution Bullet Camera can be easily programmed with its built-in joystick and on-screen display icon menu. This model offers a 3.3~12mm Varifocal Lens with DRC and HME technology.

Use the above icon menu tree as a guide when programming your Value Line Camera.

Head Office

5436 W Crenshaw Street Tampa, FL 33634
Toll Free 866-446-3595 FAX 813-888-9262

Sales Office

9551 Irvine Center Dr
Irvine, CA 92618

